

HOW TO USE



1

Open Holder while turning it counterclockwise, unlock Bottom Hook to open Bottom Cover. Then place label roll and close Holder.



2

Insert label sideways under transparent Label Pressor, turn it back onto Bottom Cover.



3

Close Bottom Cover while pushing it, then lock it with Bottom Hook turning forwards to the reverse directions of an arrow.



4

Cut backing paper, pulling it downwards as arrow indicates.



5

Pull machine toward you at the same speed with gripping motion.

CLEANING STUCK LABEL



Unscrew 2 screws. Easily remove stuck label by solvent for strong adhesive.

NOTICE

1. Unnecessary to make slit or slot on backing paper for feeding.
2. Film with less than 50 μ m thickness is unacceptable.
3. Use only die-cut labels.
4. A cotton-swab moistened with ALCOHOL, is recommended to wipe adhesive from Mecha-Sensor.

SPECIFICATIONS

MODEL	LABEL SIZE (mm)		MAX. OUTSIDE DIAMETER (mm)
	STROKE	WIDTH	
LAP65-30	20-60	20-30	100
LAP65-60		25-60	
LAP65-100		55-100	

Please contact us if your shape labels seem difficult to dispense.
We reserve the right to change specifications without notice for improvement.

US PAT. 4986874
EP PAT. 759398, 968925
JP PAT. 2708677, 2708680

